

InstruTech®

Series 3000 - The New Generation of B-RAX™ Vacuum Gauge Controllers

- 3 Channel Controller for one ionization and two convection gauges or one ionization, one convection and one alternate capacitance diaphragm gauge
- Various pressure measurement ranges from 2 x 10⁻¹¹ to 1,000 Torr
- 3 analog outputs, 6 setpoint relays, RS232/RS485 serial communications, remote Digital I/O
- Compact space saving half rack design, bench top or panel/rack mount instrument
- ♦ Outstanding product warranty of 5 years



Description

The InstruTech series 3000 B-RAX is a highly versatile vacuum gauge controller capable of operating one hot or cold cathode ionization gauge (IG) and up to two CVG101 convection vacuum gauge sensors (CG), or one IG, one CG and one alternate gauge such as a capacitance diaphragm gauge (CDG). The ionization gauge on/off, degas functions and emission current selection can be controlled via front panel soft-keys, remote input signals (Digital I/O), or serial communications. IG sensor can also be automatically turned on/off using the measurements from one of the user selectable convection or alternate gauges. When using hot cathode IGs, the B-RAX can be set to automatically switch (auto-ranging) between various emission currents. This results in optimal and stabile pressure readings over the entire measurement range from low to high vacuum. High efficiency power supply design and effective thermal management techniques are used to enable operation of the B-RAX without the need for air movement devices such as troublesome fans. The state of all setpoint relays, emission current, filament in use and error messages for all fault conditions are displayed on the easy to read OLED set-up screen. Filament operation including filament current, filament voltage, emission current and ion current can be displayed in real time to allow monitoring of filament condition.


B-RAX Controller	Ionization Gaug	Convection Gauge (CG) Compatibility		
B-RAX 3500	One CC606 UHV Cold Cathode (7.5 x 10 ⁻¹¹ to 3.75 x 10 ⁻³ Torr)	or	One CC605 Cold Cathode (1.5 x 10 ⁻⁹ to 3.75 x 10 ⁻³ Torr)	Up to two CVG101 Convection Gauges (1 x 10 ⁻⁴ to 1,000 Torr)
B-RAX 3400	One BA601 UHV Nude EB Hot Cathode	or	One BA600 Mini IG Hot Cathode	Up to two CVG101 Convection Gauges
688-9 0 0 0 158-3 1 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	(2 x 10 ⁻¹¹ to 1 x 10 ⁻³ Torr)		(1 x 10 ⁻⁹ to 5 x 10 ⁻² Torr)	(1 x 10 ⁻⁴ to 1,000 Torr)
B-RAX 3300	One BA602 Nude I ² R Hot Cathode (4 x 10 ⁻¹⁰ to 1 x 10 ⁻³ Torr)	or	One BA603 Glass I^2R Hot Cathode $(4 \times 10^{-10} \text{ to } 1 \times 10^{-3} \text{ Torr})$	Up to two CVG101 Convection Gauge: (1 x 10 ⁻⁴ to 1,000 Torr)
****** * 588-9 *** ********************************			A.	
B-RAX 3200	One IGM400 Hot Cathode (1 x 10 ⁻⁹ to 5 x 10 ⁻² Torr)	or	One CCM500 Cold Cathode (1 x 10 ⁻⁹ to 1 x 10 ⁻² Torr)	Up to two CVG101 Convection Gauges (1 x 10 ⁻⁴ to 1,000 Torr)

Specifications

measurement range:	B-RAX 3500: 7.5×10^{-11} to 1,000 Torr when used with the CC606 UHV cold cathode IG and CVG101 CG B-RAX 3500: 1.5×10^{-9} to 1,000 Torr when used with the CC605 cold cathode IG and CVG101 CG				
	B-RAX 3400: 2×10^{-11} to 1,000 Torr when used with the BA601 UHV hot cathode IG and CVG101 CG B-RAX 3400: 1×10^{-9} to 1,000 Torr when used with the BA600 hot cathode Mini IG and CVG101 CG				
	B-RAX 3300: 4×10^{-10} to 1,000 Torr when used with the BA602/603 hot cathode IG and CVG101 CG				
	B-RAX 3200: 1×10^{-9} to 1,000 Torr when used with the IGM400 hot cathode IG and CVG101 CG				
	B-RAX 3200: 1×10^{-9} to 1,000 Torr when used with the CCM500 cold cathode IG and CVG101 CG				
display pressure indication programming & set-up screen	LED - 3 independent pressure display channels - 3 digit plus 2 digit exponent per channel OLED - displays state of all setpoint relays, IG emission current, error messages for fault conditions				
units of measure	Torr, mbar, Pa - user selectable				
functionality IG	powers & operates one of the InstruTech ionization vacuum gauges listed above				
	B-RAX 3400/3300 are also capable of operating other equivalent brands of nude/glass B-A hot cathode IG				
CG	powers & operates up to 2 InstruTech CVG101 convection or Granville-Phillips® (GP) Convectron® gauges				
alternate gauge	displays pressure from one alternate gauge such as a capacitance diaphragm gauge (CDG) or other InstruTech modules using the analog input (external power source for these alternate auxiliary devices will be required)				
IG sensor control	IG sensor on/off, degas on/off and emission current (hot cathode IG) can all be controlled via front panel soft-keys, remote input signals (digital I/O) or serial communications. IG sensor can also be automatically turned on/off using the measurements from one of the user selectable convection or alternate gauges.				
IG remote input signals	IG sensor on/off, degas on/off and emission current (hot cathode IG) can also be set by applying momentary				
(digital I/O)	continuity to ground. Also the 9-pin D-sub remote input DIGITAL I/O connector provides pin-pin compatible signals with the GP 358 controller as well as compatible signals with the GP 307.				
setpoint relays / relay contact rating	six single-pole, double-throw (SPDT) / 5 A at 30 Vdc, 5 A at 250 Vac, resistive load, user assignable to any of the gauges (Note - Contact rating applies to units shipped after Nov 1, 2015, See User Manual for older units)				
analog output	three analog outputs, user assignable to any of the gauges:				
IG	log linear 0 to 10 Vdc, 1 V/decade, various scaling selections also provide analog output compatibility with Granville-Phillips® controller models 307, 350 and 358 controllers, or log Linear 1.7 V to 9.3 Vdc (nominal 1.8 to 8.7 Vdc) 0.8 V/decade, or linear 0 to 10 Vdc (useable over 3 decades, also compatible with GP 307 controller)				
combination IG + CG or IG + Alternate Gauge	log linear 0.5 to 7 Vdc, 0.5 V/decade				
CG	log linear 1 to 8 Vdc, 1 V/decade, or 0 to 7 Vdc, 1 V/decade (also compatible with GP 307, 350, 358), or non-linear analog S-curve 0.375 to 5.659 Vdc, or linear 0 to 10 Vdc (useable over 3 decades)				
analog input CDG	0-10 Vdc analog input signal from CDM900 or other brands of CDG when used as an alternate gauge to CG2, or				
InstruTech modules	analog input from InstruTech gauges: CCM501,CCM502,CVM201,CVM211,IGM401,IGM402,PCM301,WGM701				
serial communications	RS485 / RS232 - ASCII protocol - (command protocol provides compatibility with GP 307 and GP 358 controller GP350 command protocol compatibility is also available for all models except B-RAX 3500)				
status output	IG sensor on/off status message is displayed on the front panel, by serial communications and by SPDT relay (DIGITAL I/O Connector) rated at 1 A at 30 Vdc resistive, or 1 A at 30 Vac non-inductive.				
	IG degas on/off status or IG error conditions are displayed on the front panel, by serial communications and by an open collector transistor output (ground emitter) rated at 40 V max. VCE, 50 mA IC max.				
IG hot cathode filament switching	user selectable between filament 1 or 2 using the front panel soft-keys or RS232/485 serial communications				
IG hot cathode emission current	B-RAX 3400/3300: 100 μA, 4 mA, 10 mA or automatic switching (auto ranging) between 100 μA, 4 mA, 10 mA B-RAX 3200: 100 μA, 4 mA, or automatic switching (auto ranging) between 100 μA and 4 mA				
IG hot cathode degas	B-RAX 3400: 40 W, electron bombardment (EB) when used with BA601, 3 W, EB when used with BA600 B-RAX 3300: 40 W, resistive (I ² R) B-RAX 3200: 3 W, EB B-RAX 3500: N/A				
IG overpressure protection	IG sensor turns off if pressure exceeds maximum allowable pressure limit of IG				
temperature	operating: 0 to + 40 °C storage: -40 to + 70 °C				
humidity	0 to 95% relative humidity, non-condensing				
weight	1.7 lb. (0.7 kg)				
Weight.	711 IN 1011 IN				


housing		aluminum extrusion - black powder paint finish				
input power		B-RAX 3400/3300: 20 - 28 Vdc, 200 W when used with BA601, BA602 and BA603 IG				
		B-RAX 3400: 20 - 28 Vdc, 36 W when used with BA600 Mini IG				
		B-RAX 3200: 20 - 28 Vdc, 36 W B-RAX 3500: 20 - 28 Vdc, 12 W				
		B-RAX circuitry is protected against power reversal and transient over-voltages				
connectors	IG & CG	gauge cable assemblies provided by InstruTech				
	digital I/O	9-pin D-sub male				
seria	al communications	RS232: 9-pin D-sub female, RS485: 9-pin D-sub male				
analog I/O, setp	point relays, power	pluggable terminal block (mating connectors included)				
CE compliance		EMC Directive 2014/30/EU, EN55011, EN61000-6-2, EN61000-6-4, EN61326-1, EN61010-1				
environmental		RoHS Directive 2011/65/EU				

Front Panel Operation




Electrical Connections





B-RAX 3500

All connections are the same as the B-RAX 3400/3300/3200 except IG (Note IG Collector is removed below)




CC605 / CC606 Cold Cathode IG

Outline Drawing

Front View

B-RAX IG ON/OFF DEGAS CG1 Power CG2 InstruTech Torr Pa (3.08 in.)

Side View



Ordering Information Part Numbers

B-RAX Vacuum Gauge Controller

3 channel pressure display vacuum gauge controller. Operates one ionization gauge (IG) plus up to two convection gauges (CG), or one IG, one CG and one analog input from an alternate gauge such as a CDG. Includes 6 setpoint relays, 3 analog outputs, Digital I/O, RS232/RS485 serial communications.



B-RAX 3500: Operates one CC605 or one CC606 cold cathode IG plus up to two CGs B-RAX 3400: Operates one BA601 UHV nude EB-degas IG or one BA600 hot cathode Mini IG plus up to two CGs B-RAX 3300: Operates one BA602 nude or BA603 glass I²R hot cathode IG plus up to two CGs B-RAX 3200: Operates one IGM400 hot cathode IG or one CCM500 cold cathode IG plus up to two CGs

B-RAX 3400 B-RAX 3300 B-RAX 3200

B-RAX 3500

Optional 24 Vdc Power Supply for B-RAX

Connector: 2-pin pluggable terminal block to mate with the B-RAX

Compliance: CE, RoHS, UL (US/Canada), CCC (China)

Power Input: 100 - 240 Vac, 50-60 Hz

Power Output: PS330: 24 Vdc @ 9.16 A (220 W) see selection details below

PS301: 24 Vdc @ 2.5 A (60 W) see selection details below

For B-RAX 3400 / 3300 when used with BA601, BA602 and BA603 IG (Power cord with North American 115 Vac plug included)

For B-RAX 3400 / 3300 when used with BA601, BA602 and BA603 IG (No power cord included*)

P

For B-RAX 3400 when used with BA600 Mini IG, B-RAX 3500, B-RAX 3200 (Power cord with North American 115 Vac plug included)

For B-RAX 3400 when used with BA600 Mini IG, B-RAX 3500, B-RAX 3200 (No power cord included*)

PS330-UA PS330-UX

PS301-UA PS301-UX

Gauge Cable	BA601/602 IG	BA601/602 IG	BA603 IG	BA600 IG	IGM400 IG	CC605/CC606 IG	CC605 IG	CVG101 CG
	B-RAX 3400/3300	B-RAX 3400	B-RAX 3300	B-RAX 3400	CCM500 IG	B-RAX 3500	CC606 IG	All B-RAX
	Bakeable,200 °C	B-RAX 3300			B-RAX 3200	Bakeable,250 °C	B-RAX 3500	Models
		0			9		0	
10 ft. (3 m)	IRNBD441-1-10F	IRN441-1-10F	IRG441-1-10F	HMG441-1-10F	BXC400-1-10F	CCPB641-1-10F	CCP641-1-10F	CB421-1-10F
25 ft. (8 m)	IRNBD441-1-25F	IRN441-1-25F	IRG441-1-25F	HMG441-1-25F	BXC400-1-25F	CCPB641-1-25F	CCP641-1-25F	CB421-1-25F
50 ft. (15 m)	IRNBD441-1-50F	IRN441-1-50F	IRG441-1-50F	HMG441-1-50F	BXC400-1-50F	CCPB641-1-50F	CCP641-1-50F	CB421-1-50F
>50 ft.	Consult factory							

Note: The IRNBD441 <u>bakeable</u> Nude IG cable is provided with push-on sockets for connection to the Nude gauge pins (BA601/602 pins) and is bakeable to 200 °C. All other cables for hot cathode and convection gauges listed above are rated for 50 °C ambient temperature. All IG cables for hot cathode gauges listed above can be used with either single or dual filament ion gauges and filament switching is controlled from the B-RAX controller. The CCPB641 <u>bakeable</u> cold cathode IG cable is bakeable to 250 °C while the CCP641 cold cathode IG cable is rated to 80 °C.

000849
000849
001007

BA600, BA601, BA602, BA603, IGM400, CCM500, CC605, CC606 ionization gauges	See data sheets for these IG products
CVG101 convection gauge	See CVG101 Worker Bee™ convection gauge data sheet

Granville-Phillips® and Convectron® are registered trademarks of MKS Instruments, Andover, MA.



InstruTech®

1475 S. Fordham Street Longmont, CO 80503 USA Phone +1-303-651-0551 Fax: +1-303-678-1754 E-mail info@instrutechinc.com Web www.instrutechinc.com